

E 款, 反向10.6四脚, SMT-*6.20

MAPX

MODIFICATION

DATE

NOTES:

1.HOUSING: SEE NOTES, UL94V-0 .

TERMINAL: SEE NOTES.

SHELL: SEE NOTES.

SPECIFICATION:

1.ELECTRICAL CHARACTERISTIC:

CONTACT RESISTANCE: 30M Ω MAX

DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN

INSULATION RESISTANCE: 1000M Ω MIN

2.MECHANICAL CHARACTERISTIC:

INSERTION FORCE: 35N(3.57KGF) MAX

EXTRACTION FORCE: 10~35N(1.02~3.57KGF)MIN

DURABILITY: 1500 CYCLES EXTRACTION FORCE:10~35N

5000 CYCLES MIN

5000 CYCLES EXTRACTION FORCE:3~35N

3.ENVIRONMENTAL:

OPERATING TEMPERATURE: -55℃+85℃

4.Contact finish:




01:Selective Gold Flash

02:Selective Gold 3U"

03:Selective Gold 5U"

04:Selective Gold 15U"

05:Selective Gold 30U"



FRONT EDGE OF CONNECTOR
PCB LAYOUT (T=1.60mm)

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	± 0.25	X.	$\pm 5^\circ$
.X	± 0.20	.X	$\pm 2^\circ$
.XX	± 0.15	.XX	$\pm 1^\circ$
.XXX	± 0.10	.XXX	$\pm 0.5^\circ$

深圳市精拓金电子有限公司

单位

MM

制图

Z-Y-B

制图料号

913-361B2021S10200

比例

1:1

审核

产品名称

AF10.6E款四脚无边方弹铁壳反向

日期

2014.03.24

核准

角法

版本

AD

DATE

2014.03.24

APPD

VIEW

VER

AD