

HSF

NOTES:

Current Rating: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40℃ to +125℃(Au)
 -40℃ to +105℃(Sn)

Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA9T+33%G.F UL94V-0


Ordering Information

2134 - 1 XX R XX CUN X 1




No. of Pins per ROW: 02-40PIN

Contact Plating:
 G0=Gold Flash
 G3=10μ"Gold
 G4=15μ"Gold
 G5=30μ"Gold
 S0=Gold Flash/Matte Tin
 S3=10μ"Gold/Matte Tin
 S4=15μ"Gold/Matte Tin
 S5=30μ"Gold/Matte Tin
 SN=Tin
 SM=Matte Tin


Packing:
 T=Tube
 R=Tube&Reel



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



SECTION A-A



Item	Pitch	Mating
Standard	2.54	1125B
Alternate		

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DIM	TOL	DRAW	DATE	SCALE	FIT	PART NO.
A3	2020/11/30	Modify Drawing,Add VIEW&DIM.	A3	OPERATION			DRAW	DATE	SCALE	FIT	2134-1XXRXXCUNX1
A2	2016/11/10	Modify	A2	x.X	±0.40		XSR	2020/11/30	UNIT	mm	TITLE:
A1	2012/08/24	Change the mating object		x.XX	±0.25		CHECK	DATE	SIZE	A4	2.54mm FEMALE HEADER SINGLE ROW 90°DIP H=3.20
A0	2012/08/02	NEW		x.XXX	±0.15		APPROVE	DATE	SHEET	1/1	Customer NO.
				Angle	± 3°				PROJ.		

WCON
 Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com

WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com