


Ordering Information:
 A1257WV-S-XP - *** - *** - *

- 1.Part No.
 2.Material:
 (Blank):Nylon 9T,UL94V-0(Ivory)
 GWT:Nylon 9T,UL94V-0,GWT 750 °C
 3.Color:
 (Blank):Ivory
 BK:Black BL:Blue
 OR:Orange LE:Light blue
 TR:Tomato red LY:Lemon yellow
 MG:Moss green DPK:Dark pink
 4.Finish:
 (Blank):Tin over Nickel
 G:Gold over Nickel



SPECIFICATIONS:

Current Rating: 1A AC,DC
 Voltage Rating: 50V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 30mΩ Max.
 Insulation Resistance: 100MΩ Min.
 Withstanding Voltage: 100V AC/minute
 Pin Material: Phosphor Bronze/Tin over Nickel
 Material: Nylon 9T,UL94V-0(Ivory)

Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	1.25	5.75	9P	10.00	14.50
3P	2.50	7.00	10P	11.25	15.75
4P	3.75	8.25	11P	12.50	17.00
5P	5.00	9.5	12P	13.75	18.25
6P	6.25	10.75	13P	15.00	19.50
7P	7.50	12.00	14P	16.25	20.75
8P	8.75	13.25	15P	17.50	22.00

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	6:1	1 of 1
Draw By:	Approved :	
Dlankul Wan	Jack Yin	

Title :
 1.25mm PITCH
 180° Wafer - SMT TYPE

REV	DESCRIPTION	DATE	General Tolerance
A1	CHANGE THE TEMPERATURE	2019.05.21	x.xx±0.25
A0	NEW RELEASE	2018.10.23	x.xx±0.20
			x.xxx±0.15

PROJECT	⊕ ⊖
---------	-----

DRAW NO : A1257WV-S-XP REV A1