



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: -25° C~85° C;
3. 适用线规: AWG#30~#22.
4. 额定电压: 250V DC/AC(rms).
5. 额定电流: 3.0A.
6. 接触电阻: ≤20mΩ.
7. 耐压值: 1000V AC/minute.
8. 绝缘电阻: ≥1000MΩ.

Poles	Dimensions (mm)	
	A	B
1	2.50	7.50
2	2.50	7.50
3	5.00	10.00
4	10.00	12.50
5	10.00	15.00
6	12.50	17.50
7	15.00	20.00
8	17.50	22.50
9	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00
16	37.50	42.50

APPROVALS		DATE	PART NO.		TITLE:	
DRAWN	G.M.Chen	2015/7/17	XHB-□□AW		Connector	
CHECKED						
APPROVALS			XHB-□□AW			
TOLERANCES ARE			30 ^{±0.15}	±0.30	ANGLE	SHEET 1 OF 1
CHANGE.			10 ^{±0.10}	±0.20	SCALE: 1:1	PROJ.
CHECK.			5 ^{±0.10}	±0.15		
APPRO.			±2'			
ECN NO.	REV.	DATE.	DESCRIPTION.		NEW	

DEALON 德之隆®
ELECTRONICS CO.,LTD