

| REVISION | DESCRIPTION | DATE | DRAFTER |
|----------|---------------|----------|---------|
| A0 | FIRST RELEASE | 21.11.22 | SQW |
| | | | |

A

A

B

B

C

C

D

D

E

E

F


F

G


G

H

H



1/4±0.010 [1.0]*



产品单重: 9.50g

技术要求:

- 1 电气特性: 特性阻抗:50Ω; 增益(Gain) 2dBi
适用频率范围:2.4GHz-2.5GHz VSWR:2.0 MAX;
5.15GHz-5.85GHz VSWR:2.5 MAX;
- 2 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
- 3 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污;
镀层色泽光亮均匀, 不得有氧化。
- 4 包装规范: 50PCS/包
- 5 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

| | | | | |
|-----|---------------|---------------------------------|-------|---------|
| 9 | 2TB050BK1-020 | OD:5.0*L20.0mm, 无卤阻燃, 超薄型热缩套管黑色 | 1 | --- |
| 8 | 2YGxxx | 钢管: OD5.00*L23.0*OD0.60mm, 材质黄铜 | 1 | --- |
| 7 | 2YGxxx | 钢管: OD5.00*L23.0*OD1.55mm, 材质黄铜 | 1 | --- |
| 6 | 2SBKG0200 | 套杆, L67.5*09.35, TPEE 黑色 | 1 | --- |
| 5 | 2SBKU32N3 | 上固定座, Ø9.35*L28.8, PC 黑色连铆钉式 | 1 | --- |
| 4 | 2SBKD34N2 | 下固定座小孔, Ø9.35*L19.7*Ø5.10, PC黑色 | 1 | --- |
| 3 | 2LC15PF801-5 | SMA 母针镀金Ø1.5*L7.8mm, 镀金3u'' | 1 | --- |
| 2 | 2LC15PM808-8 | SMA公头Ø10.0*L16.5*Ø5.1mm, 黑色POM | 1 | --- |
| 1 | 2C5R17811BN1 | 微细同轴电缆, RG178, 银锡线, 棕色 | 1 | --- |
| No. | PART NUMBER | PART NAME & DESCRIPTION | Q' TY | REMARKS |

| | | |
|---|---|---|
| GENERAL TOLERANCE: LINEAR: X ± 2.00 X. X ± 1.00 X. XX ± 0.50 X. XXX ± 0.30 ANGLE: X° ± 4.00° X. X° ± 3.00° X. XX° ± 2.00° X. XXX° ± 1.00° | HJ-Tech FILE NAME: 产品图 ENG/DATE: SQW/21.11.22 ANGLE: X° ± 4.00° X. X° ± 3.00° X. XX° ± 2.00° X. XXX° ± 1.00° | 东莞市皇捷通讯科技有限公司 TITLE: 射频天线组件 2dBi WiFi 双频天线, OD379黑色, RG178线+SMA公头母针, OD:10*108mm P/N: RF2111026 UNIT: mm SCALE: 1:1 REVISION: A0 SHEET: 1/1 |
|---|---|---|

COMPLIANCE WITH THE REQUIREMENT: RoHS; HF; SONY SS-00259; OTHERS
*NO USING ESTRICITED AND BANNED SUBSTANCE