

环保物料

TEL: 0769-82001899

SPECIFICATIONS

- 1.Voltage rating: 125V AC, DC
- 2.Current rating: 1A, AC, DC
- 3.Withstanding Voltage: 500V AC/minute
- 4.Insulation resistance:100M min
- 5.Temperature range: -25 ° C-+85 ° C
- 6.Contact resistance: 20m max

WAFER

Housing Material: LCP UL 94V0





Pin Material: Phosphor Bronze or Brass

Contact Area Plating: Plated Tin or Plated Gold
Mates with :P1250 series Housing

Poles:02-20P

Part No.: M1250RS-xxP

Pin位数



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
02	1.25	7.35
03	2.50	8.60
04	3.75	9.85
05	5.00	11.10
06	6.25	12.35
07	7.50	13.60
08	8.75	14.85
09	10.00	16.10
10	11.25	17.35
11	12.50	18.60
12	13.75	19.85
20	23.75	29.85

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO.,LTD.	SHEET	1/1	
				X.	±0.30	X°	±5°		CHKD	DATE	2020.04.12
				.X	±0.20	.X°	±2°		APPD	UNITS	mm
				.XX	±0.08	.XX°	±1°		VIEW	SCALE	1:1
AO	MODIFICATION			DRAW	DATE			PRODUCT NAME	1.25mm Crimp Style Connectors		
VER								PART. NO.	M1250RS-xxP		
1	2	3	4	5	6	7	8	9	10	DWG. NO.	009