



环保物料

TEL:0769-82001899



PIN ASSIGNMENT:



*MATERIAL (IDC)

INSULATOR:PBT (UL 94V-0)

Contact: Copper Alloy.

Contact Plated: Gold or Tin over
Nickel Plated.

*SPECIFICATIONS

TEMPERATURE RANGE: -20°C TO +105°C

CONTACT RESISTANCE: 3Ω MAX.

INSULATION RESISTANCE: 5MΩ MIN.

WITHSTANDING VOLTAGE: 300V 10S

OF TRANSPORT DIVISION:

序号	名 称	规 格 说 明	数量
1	端 子	IDC-XP 二件式 (2.00mm)	2
2	电 线	2651 28# 1.00间距灰排 7/0.12TS	30P
3	卡 扣	反扣20P (2.00mm)	2

How to order :										
CL	200	X	X	XX	XXX	X	XX	X	X	X
Product Name: HDC F:FD CL:IDC Cable CL:IDC+FD Cable	Pitch: 1.27mm 2.00mm 2.54mm	Number of Row: 1:Single 2:Double Row	Product Number: 2:Two piece Type 3:Three Piece Type 4:With battery holder	NO OF Pins Per Row:01~40P	Length of Cable: Q:No Cable XXL=XXmm	Contact Plated: B:Half gold tin Q:ALL gold	Terminal Type: C:Common H:High tension S:Single contact Y:Double contact	Colour: 1:Black 2:Gray 3:Other	Cable Material: Q:Common 6:265/0.161S 8:285/0.127TS	Packing: E:PE Bag P:Package T:Tube packing R:Roll packing

TOLERANCE UNLESS OTHERWISE				DRAWN	CK tan	XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO.,LTD.			SHEET	1/1
X.	±0.30	X°	±5°	CHKD					DATE	2020. 04. 12
.X	±0.20	.X°	±2°	APPD		PRODUCT NAME			UNITS	mm
.XX	±0.08	.XX°	±1°	VIEW	⊕	PART. NO.			SCALE	1:1
.XXX	±0.03	.XXX°	±0.5°			CL200233019BC10E			DWG NO.	009

1	2	3	4	5	6	7	8	9	10
---	---	---	---	---	---	---	---	---	----