



环保物料

TEL: 0769-82001899



SPECIFICATIONS

- 1.Voltage rating: 250V AC, DC
- 2.Current rating: 3A, AC, DC
- 3.Withstanding Voltage: 1000V AC/minute
- 4.Insulation resistance:1000M min
- 5.Temperature range: -25 ° C~+85 ° C
- 6.Contact resistance: 10m max

WAFER

Housing Material: Nylon UL 94V-0 (2)

Pin Material: Phosphor Bronze or Brass


Contact Area Plating: Plated Tin or Plated Gold

Mateswith:M2501□ series□ header

Poles:02-15P

Part No.: B2501V-xx-N0

Pin位数



编 号	尺寸 (mm)	
	A	B
02P	2.50	7.50
03P	5.00	10.00
04P	7.50	12.50
05P	10.00	15.00
06P	12.50	17.50
07P	15.00	20.00
08P	17.50	22.50
09P	20.00	25.00
10P	22.50	27.50
11P	25.00	30.00
12P	27.50	32.50
20P	47.50	52.50

PCB LAYOUT

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO.,LTD.	SHEET	1/1
				X. ±0.30	X° . ±5°	CHKD			DATE	2020.04.12
				.X ±0.20	.X° ±2°	APPD			UNITS	mm
				.XX ±0.08	.XX° ±1°	VIEW	⊕		SCALE	1:1
AO				.XXX ±0.03	.XXX° ±0.5°	PRODUCT NAME	2.50mm Crimp Style Connectors	DWG NO.	009	
VER	MODIFICATION	DRAW	DATE			PART. NO.	B2501V-xx-N0			