








Rating:7A 20V DC
Contact Resistance:100 m Ω Max.
Operating temperature:-20 $^{\circ}$ C~70 $^{\circ}$ C
Operating force:3~20N
Operating Life:5,000cycles

⑥	round	1	SUS	Natural
⑤	Shielding	1	Brass	Ag-Plated
④	PIN	1	Brass	Au-Plated
③	Terminal	1	SUS	Ni-Plated
②	Tip Spring	1	Copper alloy	Ni-Plated
①	Body	1	Pa6t	Black
ITEM	PART NAME	QTY.	MATERIAL	FINISHING

APPROVALS		DATE	PART NO.		DC JACKS
DRAWN	G.M.Chen	2015/3/20	ELECTRONICS CO.,LTD		
CHECKED			TITLE:		DC JACKS
APPROVALS			PART NO.		DC-D193
TOLERANCES ARE		30~0.1 10~0.30 5~10 ~5	±0.30 ±0.20 ±0.15 ±0.10	ANGLE	UNIT: mm
			±2°		SCALE: 1:1
					SHEET 1 OF 1
					PROJ. ①
ECN NO.	REV.	DATE.	DESCRIPTION.		
	A		NEW		