



Schematic



PIN	ø100	ø130
APPD.		

Rating: 0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles



ITEM	PART NAME	QTY.	MATERIAL	FINISHING
④	PIN	1	BRASS	Ag-Plating
③	CURVE PIECE	1	BRASS	Ag-Plating
②	Spring	1	SUS301	Ag-Plating
①	HOUSING	1	FR52	

APPROVALS		DATE	TITLE:	
DRAWN	G.M.Chen	2018/3/15	DC JACK	
CHECKED				
APPROVALS				

DEALON 德之隆
 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	SHEET	PROJ.
	A		NEW				30~0.1±, ±0.30	±2°	mm	1:1	1 OF 1	
							10~0.30 ±0.20					
							5~0.10 ±0.15					