


A=2.0* n P+0.50±0.30
 B=2.0* n P-2.0±0.20
 Pin Number=2~80

Technical Data
 Material:
 Contact material: Phosphor bronze
 Plating: Gold Flash
 Insulator material: Black polyester UH94V-0
 Standard: PA6T+30%G.F



Electrical:
 Current rating: 1.5amps/contact max.
 Contact resistance: $\leq 20m\Omega$ /contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding voltage: 450V AC/minute
 Mechanical:
 Soldering temperature: +260°C, 4s max
 UNSPECIFIED TOLERANCE: ± 0.20



PCB Layout

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	DW200R-22-XX-45	
CHECKED			CONNECTOR	
APPROVALS			PART NO.	SCALE: 1:1
			UNIT: mm	SHEET 1 OF 1
			ANGLE	PROJ.
			$\pm 2^\circ$	
			TOLERANCES ARE	
			30 \pm 0.15	
			10 \pm 0.30	
			5 \pm 0.10	
			± 0.10	
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	

DEALON 德之隆
 ELECTRONICS CO.,LTD