



PCB Layout



Technical Data
 Material: Brass
 Contact material: Brass
 Plating: Gold Flash
 Insulator material: Black polyester UL94V-0
 Standard: 6T+30%G.F

Electrical:

Current rating: 1.5amps/contact max.
 Contact resistance: $\leq 20m\Omega$ /contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding voltage: 450V AC/minute

Mechanical:

Soldering temperature: +260°C, 4s max
 UNSPECIFIED TOLERANCE: ± 0.20

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	D/2200R-22-XX-39	
CHECKED			CONNECTOR	
APPROVALS			PART NO.	D/2200R-22-XX-39
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE
		10 ^{±0.10}	±0.20	UNIT: mm
		5 ^{±0.10}	±0.15	SCALE: 1:1
				SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	PROJ.
	A		NEW	

