


A=1.27* $\frac{DP}{2}$ ±0.4±0.3
 B=1.27* $\frac{DP}{2}$ -1.27±0.2
 Pin Number=4 ~ 100

Technical Data
 Material:
 Contact material: Phosphor bronze
 Plating: Gold Flash
 Insulator material: Black polyester UL94V-0
 Standard: PA6T+30%G.F



Electrical:
 Current rating: 1.0Amps/contact max.
 Contact resistance: ≤20mΩ/contact
 Insulation resistance: ≥1000MΩ at V=100V
 Withstanding voltage: 300V AC/minute
 Mechanical:
 Soldering temperature: 260°C, 10s max
 UNSPECIFIED TOLERANCE: ±0.20



PCB Layout

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	DW127R-22-XX-34	
CHECKED			CONNECTION	
APPROVALS			PART NO.	
TOLERANCES ARE		ANGLE	UNIT:	SCALE:
30 ^{±0.15}	±0.30	±2°	mm	1:1
10 ^{±0.10}	±0.20			SHEET 1 OF 1
5 ^{±0.10}	±0.15			PROJ
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	

DEALON 德之隆
 ELECTRONICS CO.,LTD