



SPECIFICATION

Current rating: 5A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20m Ω max.
 Withstand voltage: 1500V AC/min.
 Insulation resistance: 1000M Ω/min.
 Temperature range: -25℃~+85℃

Material:

Post:Brass.Tin/plated
 Base:Nylon66 UL94V-0 or V-2

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	TITLE:			
CHECKED:	DATE:	3962S-3P 空中間P			
DRAWN:	DATE:	CLIENT P/N	C2940218	UNIT	mm
LZH	2014-10-06	FILE NO.	Chantrw-3962-0022	SCALE	Free
		REV.	A	WD000	

深圳市灿科盟实业有限公司
 CHANKEMENG INDUSTRY CO., LTD