



SPECIFICATION

Current rating: 5A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20m Ω max.
 Withstand voltage: 1500V AC/min.
 Insulation resistance: 1000M Ω/min.
 Temperature range: -25℃~+85℃

Material:

Post:Brass.Tin/plated
 Base:Nylon66 UL94V-0 for V-2

APPROVED:	DATE:				
CHECKED:	DATE:	TITLE: 3962S-8P 空第2, 4, 6, 8P			
DRAMM:	DATE:	CLIENT P/N	C2940224	UNIT	mm
LYP	2018-04-07	SCALE	Free	REV.	A
TOLERANCE TABLE		FILE NO.	Chantw-3962-0032	WD000	
.0	±0.30				
.00	±0.20				
.000	±0.05				