



SPECIFICATION

Current rating: 5A AC/DC

Voltage rating: 250V AC/DC

Contact resistance: 20m Ω max.

Withstand voltage: 1500V AC/min.

Insulation resistance: 1000M Ω/min.

Temperature range: -25℃~+85℃

Material:

Post:Brass.Tin/plated

Base:Nylon66 UL94V-0 or V-2

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 3962S-4P 空第2, 3P			
DRAWN: LYF	DATE: 2008-04-07	CLIENT P/N	C2940220		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-3962-0033	REV.	A