


P.C.B LAYOUT

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED				REVISIONS		PRO.AGI.	REV
						UP TO 5mm: ±0.1	ANGULAR ±1°	NO	DATE	UNIT : MM	ROHS COMPLIANT	DWN	BY
						ABOVE 5mm: ±0.2				SCALE: 1:1		CHK'D	APPD
6		右长针	BRASS	1	Cu-PLATED/Sn-PLATED			1					
5		左长针	BRASS	1	Cu-PLATED/Sn-PLATED								
4		右短针	BRASS	1	Cu-PLATED/Sn-PLATED								
3		左短针	BRASS	1	Cu-PLATED/Sn-PLATED								
2		后盖	PBT	1	BLACK								
1		底座	PBT	1	BLACK								
 <b>HAOYU(HONGKONG)LIMITED</b> 皓宇(香港)有限公司													
						TITLE: DIN SOCKET							
						MODEL: DIN-422A							