



PIN	Ø2.0	Ø2.5	Ø3.0
DIM A	Ø6.3±0.05	Ø6.3±0.05	Ø6.55±0.05
DIM B	Ø2.05±0.08	Ø2.55±0.08	Ø3.05±0.08

Model No.	DC-062	DC-062-1
Schematic		
CIRCUIT DIAGRAM		

NO.	PART	NAME	MATERIAL	QTY	FINISHING
6	Shunt Terminal	BRASS	Ag/Sn-PLATED	1	
5	Tip spring	SUS	Ag/Sn-PLATED	1	
4	Center pin terminal	BRASS	Ag/Sn-PLATED	1	
3	Center pin	BRASS	Sn PLATED	1	
2	Cover	PBT	BLACK	1	
1	Housing	PBT	BLACK	1	

TOLERANCE UNLESS SPECIFIED		REVISIONS	
UP TO 5mm: ±0.1	ANGULAR ±1°	NO	DATE
ABOVE 5mm: ±0.2		1	

TITLE:DC JACK		MODEL:DC-062	
UNIT : MM	SCALE: 3:1	ROHS COMPLIANT	DWN
HAOYU(HONGKONG)LIMITED	皓宇(香港)有限公司	CHK'D	BY
PRO.AGT.		APPD	APPD
REV :A0			