




### Right Angle Type




Voltage rating:500V AC/DC  
 额定电压:500V AC/DC  
 Current rating:1.0A  
 额定电流:1.0A  
 Insulation resistance:1000MΩ Min  
 绝缘电阻:1000MΩ Min  
 Withstanding voltage:≥500V AC/minute  
 耐压:≥500V AC/分钟  
 Temperature range:-40°C-+105°C  
 使用温度:-40°C-+105°C

X1270 W R -2xXX A2 - 6T V01  
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:W-wafer
- ③ Welding Board Angle:R- Straight 90°
- ④ Row No.-Pin No.:2xXX-2x04P~2x40P
- ⑤ A2:1.27x2.54mm No gaps
- ⑥ Material:6T-Nylon PA6T UL94V-0
- ⑦ Planting Category:V01-All Gold Flash



P.C.B Layout



positor	A	B	C
2x04	12.64	11.04	3.81
2x05	13.91	12.31	5.08
2x06	15.18	13.58	6.35
2x07	16.45	14.85	7.62
2x08	17.72	16.12	8.89
2x10	20.26	18.66	11.43
2x13	24.07	22.47	15.24
2x15	26.61	25.01	17.78
2x17	29.15	27.55	20.32
2x20	32.96	31.36	24.13
2x22	35.50	33.90	26.67
2x25	39.31	37.71	30.48
2x30	45.66	44.06	36.83
2x33	48.20	46.60	39.37
2x34	50.74	49.14	41.91
2x40	58.36	56.76	49.53

广东星坤科技股份有限公司

生 日期  
 效 日期  
 文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	REVISIONS
					UNSPECIFIED TOLERANCES



DSND		SCALE: N/A	MODEL TYPE: 1.27x2.54mm
DWN		VIEW:	PART NO.: X1270WR-2xXXA2-6TV01
CHKD		UNIT: mm/in	DWG NO.: X-X1270WR-2xXXA2-6TV01
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO.,LIMITED