



### SPECIFICATION

Current rating: 5A AC/DC

Voltage rating: 250V AC/DC

Contact resistance: 20m  $\Omega$  max.

Withstand voltage: 1500V AC/min.

Insulation resistance: 1000M  $\Omega$ /min.

Temperature range: -25°C ~ +85°C

### Material:

Part No: 2~12

Post: Brass Tin/plated

Base: Nylon66 UL94V-0 or V-2

Poles	Part NO.	Dimension (mm)	
		A	B
2P	W-3962S02P-0000	3.96	7.92
3P	W-3962S03P-0000	7.92	11.88
4P	W-3962S04P-0000	11.88	15.84
5P	W-3962S05P-0000	15.84	19.80
6P	W-3962S06P-0000	19.80	23.76
7P	W-3962S07P-0000	23.76	27.72
8P	W-3962S08P-0000	27.72	31.68
9P	W-3962S09P-0000	31.68	35.64
10P	W-3962S10P-0000	35.64	39.60
11P	W-3962S11P-0000	39.60	43.56
12P	W-3962S12P-0000	43.56	47.52
13P	W-3962S13P-0000	47.52	51.48

#### TOLERANCE TABLE

.0	$\pm 0.30$
.00	$\pm 0.20$
.000	$\pm 0.05$

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 3962S-7P			
DRAWN:	DATE:	CLIENT P/N	C2940223		
LYF	2008-04-07	UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-3962-0020	REV.	A WDOO