



P.C.B LAYOUT

Specifications:
 规格:
 Voltage rating:100V AC/DC
 额定电压: 100V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:800V AC/minute
 耐受电压: 800V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤10mΩ
 接触电阻: ≤10mΩ
 After environmental testing:≤20mΩ
 环境测试后: ≤20兆欧

- X2081 W V-2xXX- N0 SN
 ① ②③ ④ ⑤ ⑥
- ① Series No.
 - ② Category: W-WAFER
 - ③ Wedding Board Angle: V-Stright 90°
 - ④ Row No.-Pin No.: 2xXX-2x05~20P
 - ⑤ Material : N0-PA66 94V-0
 - ⑥ Plating Category: Sn-Bright Tin Plating



Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2*05	12.00	8.00	10.70	7.30	2*13	28.00	24.00	24.70	9.20
2*06	14.00	10.00	12.70	9.20	2*14	30.00	26.00	26.70	9.20
2*07	16.00	12.00	14.70	9.20	2*15	32.00	28.00	28.70	9.20
2*08	18.00	14.00	16.70	9.20	2*16	34.00	30.00	28.70	9.20
2*09	20.00	16.00	18.70	9.20	2*17	36.00	32.00	30.70	9.20
2*10	22.00	18.00	20.70	9.20	2*18	38.00	34.00	32.70	9.20
2*11	24.00	20.00	22.70	9.20	2*19	40.00	36.00	34.70	9.20
2*12	26.00	22.00	24.70	9.20	2*20	42.00	38.00	36.70	9.20

X2081WV-XX-N0SN	Nyln 66 UL 94V-0	Brass	Tin-Plated	X2081H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

△建 日期
 △教
 △文

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
					ANGLAR ±5°
					L≤4 ±0.2
					4<L≤16 ±0.3
					16<L≤63 ±0.4
					L>63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: X2081WV-XX-N0SN
DWN	DATE	VIEW:	PART NO.: 2.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0