



电路图

Operating force	
100gf±40gf	
130gf±40gf	
160gf±40gf	
260gf±50gf	✓
350gf±50gf	

高度	PCS/盘
H=2.5mm	1500
H=2.7mm	1500
H=3.1mm	1500
H=3.4mm	1500
H=3.7mm	1500
H=3.8mm	1500
H=4.3mm	1500
H=4.8mm	1000
H=5.0mm	1000
H=5.2mm	1000
H=5.5mm	1000

皓宇电子
HOOYA ELECTRONICS

PCB板焊盘尺寸



贴面脚长度 L
L=8.5mm
L=8.8mm

TRAVEL: 0.25 ± 0.1mm

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED	3	2021.6.30	更新图纸	WM	
5	CONTACT	SUS	1	Ag-Plated	UP TO 5mm: ±0.1	ANGULAR	2020.12.22	新增尺寸	WM	
4	CONTACT FOOT	BRASS	2	Ag-Plated	ABOVE 5mm: ±0.2	±1°	2020.12.16	更新图纸		
3	COVER	SUS	1				NO	DATE	REVISIONS	
2	BUTTON	PPA	1						BY	
1	HOUSING	PPA	1	BLACK					APPD	
					TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN	
					MODEL: TS-1157A-025E		SCALE: 1:1		CHK'D	
					HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD	
					PRO.AGL:				REV :A3	