



PCB板焊盘尺寸



Travel: 0.15 ± 0.1mm



电路图

| Operating force | |
|-----------------|---|
| 100gf±40gf | |
| 130gf±40gf | |
| 160gf±40gf | |
| 260gf±50gf | ✓ |
| 350gf±50gf | |

| 高度 | PCS/盘 |
|-----------|-------|
| H=1.5mm | 4000 |
| H=1.6mm | 4000 |
| H=1.7mm | 4000 |
| H=2.0mm | 3000 |
| ✓ H=2.5mm | 3000 |
| H=3.0mm | 2500 |

| | | | | | TOLERANCE UNLESS SPECIFIED | | | | | | | | | |
|-----|---------------------|----------|-----|------------|---|-------------|----|------------|----------------|-------|----|----------|--|---------|
| 6 | TERMINAL | BRASS | 4 | Ag-plating | UP TO 5mm: ±0.1 | ANGULAR ±1° | 1 | 2021.4.21 | 更新图纸 | | WM | | | |
| 5 | CASE | LCP | 1 | Black | ABOVE 5mm: ±0.2 | | NO | DATE | REVISIONS | | BY | APPD | | |
| 4 | CONTACT | SUS301 | 1 | Ag-plating | TITLE: TACT SWITCH | | | UNIT : MM | ROHS COMPLIANT | DWN | | | | |
| 3 | Waterproof membrane | PI | 1 | Yellow | MODEL: TS-1187-025E | | | SCALE: 1:1 | | CHK'D | | | | |
| 2 | COVER | SUS304 | 1 | White | HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司 | | | | | | | APPD | | |
| 1 | STEM | BRASS | 1 | Yellow | | | | | | | | PRO.AGL: | | REV :A1 |
| NO. | PART NAME | MATERIAL | QTY | FINISHING | | | | | | | | | | |