





环保物料

TEL:0769-82001899



Specifications

Current Rating: 3Ampere

Insulation Resistance: 1000MΩ MIN.

Dielectric Withstading: 600V AC

Contact Resistance: 20mΩ Max.

Operating Temperature: -40°C to +105°C

Material

Contact Material: Copper Alloy

Contact Plating: Gold/Tin Over Nickel

Insulator: Glass Filled Polyester

PBT (UL 94V-0)

No. of Pins/Row	Dimension	
	A	B
06	5.08	15.27
08	7.62	17.81
10	10.16	20.35
12	12.70	22.89
14	15.24	25.43
16	17.78	27.97
18	20.32	30.51
20	22.86	33.05
12	27.94	38.13
26	30.48	40.67
30	35.56	45.75
34	40.64	50.83
40	48.26	58.45
50	60.96	71.15
60	73.66	83.85
64	78.74	88.93

TOLERANCE UNLESS OTHERWISE

X.	±0.30	X°	±5°
.X	±0.20	.X°	±2°
.XX	±0.08	.XX°	±1°
.XXX	±0.03	.XXX°	±0.5°

DRAWN CK tan

CHKD
APPD
VIEW

**XFCN** 兴飞连接器有限公司  
XFCN CONNECTORS CO.,LTD.

PRODUCT NAME 2.54mm Box Header Connectors

PART. NO. BH254R-xxP

SHEET 1/1

DATE 2020.04.12

UNITS mm

SCALE 1:1

DWG NO. 009

AO

VER

MODIFICATION

DRAW

DATE