




Material 材料
 Insulator 塑胶: Glass filled PBT, (UL 94V-0)
 Contact 端子: Brass 黄铜
 Screw 螺丝: 5+7
 Electrical Characteristics 电气特性
 Current rating 额定电流: 2.5AMP
 Dielectric Withstanding Voltage 耐压:
 AC 500V for 1 Minute.
 Insulator Resistance 绝缘电阻:
 1000MΩ Min. AT DC 500V.
 Contact Resistance 接触电阻: 20MΩ Max.
 Operating Temperature 工作温度: -40℃ ~ +105℃



PIN	尺寸	A±0.15	B±0.2	C±0.2	D±0.1	E±0.2
义叉DP-9P		16.50	25.00	30.80	12.50	19.20
义叉DP-15P		24.80	33.30	39.20	12.50	27.80
义叉DP-25P		38.55	47.10	53.10	12.50	41.20
义叉DP-37P		54.90	63.50	69.44	12.50	57.30

未注公差尺寸			D-sub solder type		上海洲日电子有限公司			
尺寸	公差		义叉DP-9P/15P/25P/37P		Shanghai Zhouri Electronics CO.,LTD			
	长度	角度	Female		上海康司玛电子设备进出口有限公司			
X.	±0.3	±5°			Shanghai KangSiMa Eletronic Equipment		import and export Co.,LTD	
X.X	±0.2	±3°	版本号	20171018 A/0	TEL:86-21-34975176/51571121			
X.XX	±0.15		图纸编号	ZR20171018-DP-82				
绘图	周元金	201171018	物料编号					
审核	张海娜	201171018			1:1		mm	图幅 A4
核准	章妹	20181111					: 1	1