






备注：
套垫圈，拧螺母。





Rating: 400mA 32VAC \100mA 50VDC
125mA 125VAC

Contact Resistance: 50mΩ MAX.
Insulation Resistance: 100MΩ min.at 500VDC
Dielectric Strength: 1000 VAC rms.
Electrical life: 50,000 cycles
Operating Temperature: -20°C~80°C
Operating Pressure:2~5N
Operating Stroke:1.5~2.5mm
Protection Grade:IP65
Soldering:300°C max.for 5 seconds
Function:(ON)-OFF

MATERIAL:

Cover:Nylon66,UL rated:94V-2 min
Base:Nylon66,UL rated:94V-2 min
Terminal:Brass,

CUT-OUT



				 D-SWITCH[®] 东莞市德松电子有限公司 D-SWITCH ELECTRONICS CO.,LTD								
				公差 TOLERANCES		.X± 0.5	.XX± 0.3	角度 ANGLE ±1°		单位 DIMENSION UNIT		mm.
				版本 VERSION	A0	比例尺 SCALE	1:1	日期 DATE	2021.08.31	品 名 TITLE		图 号 DRAWING NO
				核 准		核 对		绘图	孙成	PB-12M11-RPBN-FA		1020005
版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	APPROVED BY		CHECKED BY		DRAWN BY	孙成	PB-12M11-RPBN-FA		1020005