




TYPE-2加前铆（不通孔）

TYPE-3加后铆（通孔）



Specifications:

规格:

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:500 AC/minute

耐受电压: ≥ 500V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -55℃-+85℃

Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

Contact resistance:30mΩMAN

接触电阻: ≤30mΩ

Material:

材料:

Contacts:Brass Gold Plated

接触: 黄铜镀金

Insulator:PBT+30%

绝缘体: PBT+30%

Shell (Fead) :Spcc

外壳: 铁

X04 XX W X X X X
① ② ③ ④ ⑤ ⑥ ⑦

① Series NO.

② Row No.Pin No.XX-09;15;25;37

③ Welding Board Angle :W-male

④T: Tradutional C: Car-pin

⑤Planting Categoty: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7 : AuSn

⑥B:BLACK W:White BL:Blue Y:Yellow G:Green R:Red

⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5; 6:TYPE-6

NO.POS	A	B	C	D	E
15PIN	16.92	24.99	30.80	19.00	2.29
26PIN	25.25	33.32	39.20	27.65	2.29
44PIN	38.96	47.04	53.10	41.20	2.29
62PIN	55.42	63.50	69.40	57.44	2.29

DSND		DATE		SCALE: N/A	MODEL TYPE:		
DWN		DATE		VIEW: 	PART NO.:		
CHKD		DATE		UNIT: mm/in	DWG NO.:		
APPD		DATE		SIZE: A4	X04XXWXXXX		
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
					1.0g	1/1	A0

					units: mm
Δx					tolerance:
Δx					X.X ±0.2mm
Δx					X.XX ±0.1mm
MARK					X.XXX ±0.05mm
REVISIONS					UNSPECIFIED TOLERANCES
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					