





3D VIEW

Specifications:

规格:

Current rating:5A AC/DC

额定电流: 5A AC/DC

Voltage rating:500V AC

额定电压: 500V AC

Withstanding voltage:500V AC/MIN

耐受电压: ≥500V AC/分钟

Temperature range:-25℃-+105℃

温度范围: -55℃-+105℃

Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

Contact resistance:30mΩMAN

接触电阻:≤30mΩ

Material And FINISHED:

材料和成本:

INSULATOR:PBT+30 % GF UL 94V-0

绝缘体: pbt+30 % gf ul 94-0

SHELL:STEEL, NI FINISHED

外壳: 钢、聂加工

CONTACT MATERIAL:BRASS SELEVITE GOLD FINISHED

触点材料: 黄铜SELEVITE

X03 XX F X X X X

① ② ③ ④ ⑤ ⑥ ⑦

① Series NO.

② Row No.Pin No.XX-09;15;25;37

③ Welding Board Angle :F-Fmale

④ T: Tradutional C: Car-pin

⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn

⑥ B:BLACK W:White BL:Blue Y:Yellow G:Green R:Red

⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5; 6:TYPE-6

NO. OF CONTACT	A	B	C
09	30. 80	24. 99	16. 35
15	39. 20	33. 30	24. 75
25	53. 05	47. 04	38. 35
37	69. 40	63. 50	54. 75

铆合方式	TYPE-1: 铆合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 铆合锁螺丝
图式				

						DSND		DATE		SCALE: N/A	MODEL TYPE:		
Δ X					units: mm	DWN		DATE		VIEW: 	PART NO.:		
Δ X					X.X ± 0.2 mm	CHKD		DATE		UNIT: mm/in	DWG NO.: X03XXFXXXX		
Δ X					X.XX ± 0.1 mm	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION		DATE	REVISED	APPROVED	X.XXX ± 0.05 mm							
REVISIONS						UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											WEIGHT 1.0g	SHEET 1/1	REVISION A0

					units: mm
ΔX					tolerance: X.X
ΔX					±0.2mm
ΔX					X.XX ±0.1mm
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm

REVISIONS

UNSPECIFIED TOLERANCES

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn