




Specifications:
规格:
Current rating:5A AC/DC
额定电流: 5A AC/DC
Voltage rating:250V AC
额定电压: 250V AC
Withstanding voltage:500V AC/MIN
耐受电压: ≥500V AC/分钟
Temperature range:-25℃~+105℃
温度范围: -55℃~+105℃
Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
Contact resistance:30mΩMAN
接触电阻:≤30mΩ
Material And FINISHED:
材料和成本:
INSULATOR:PBT+30% GF UL 94V-0
绝缘体: pbt+30% gf ul 94-0
SHELL:STEEL, NI FINISHED
外壳: 钢、镍加工
CONTACT MATERIAL:BRASS SELEVITE GOLD FINISHED
触点材料: 黄铜SELEVITE

X03 XX W X X X X
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
② Row No. Pin No.XX-09;15;25;37
③ Welding Board Angle :W-male
④ T: Tradutlional C: Car-pin
⑤ Planting Categoty: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7 : AuSn
⑥ B:BLACK W:White BL:Blue Y:Yellow G:Green R:Red
⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5; 6:TYPE-6

NO OF CONTACT	A	B	C
09	30. 81	24. 99	16. 92
15	39. 14	33. 32	25. 25
25	53. 04	47. 04	38. 96
37	69. 32	63. 50	55. 42

铆合方式	TYPE-1: 铆合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 铆合锁螺丝
图式				

						DSND		DATE		SCALE: N/A	MODEL TYPE:			
					units: mm	DWN		DATE		VIEW: 	PART NO.:			
Δx					tolerance:	CHKD		DATE		UNIT: mm/in	DWG NO.: X03XXWXXXXX			
Δx					X.X ±0.2mm									
Δx					X.XX ±0.1mm									
MARK	DESCRIPTION		DATE	REVISED	APPROVED	X.XXX ±0.05mm	APPD		DATE		SIZE: A4			
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						1.0g						1/1	A0	