






RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.2±0.15mm
Storage Temperature	- 30° C to 85° C

Mechanical

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR
E	Button	PPA	1	Black
D	COVER	Brass	1	Cleaning
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag

Type	Operating Force (gf)	Height (mm)	Button	Leads Shape (G, J, T)	Ground pin (0, 1)	Pegs Option (0, 1)
YTS1H015	250±50	**	B (BLACK)	T	0	0 (None)
		P 9.5				
		N 9.0				
		M 8.0				
		L 7.5				
		K 7.0				
		J 6.5				
		H 6.0				
		G 5.5				
		F 5.0				
	160±50	E 4.8				
		D 4.5				
		C 4.3				
		B 3.8				
		A 3.5				

X. ±0.50	X. ° ± 2°	UNITS mm
. X ±0.30	. X° ± 1°	MAT'L
. XX ±0.10	. XX° ± 0.5°	
. XXX ± 0.05		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH
		Q' TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO., LTD


PART NO.
YTS1H016

TITLE:
TACTILE SWITCH

APPD: ROGER

DWG NO. :
YTS1H016

CHKD: ROC
DR: BILLY WANG 2020/08/21



SCALE SHEET REV.
1/1 1/1 A1

Packaging:
1000 pieces