







N=PIN数



P.C.B LAYOUT

Material 材料
 Insulator 塑胶: PBT (UL 94V-0)
 Contact 端子: Brass 黄铜
 Contact plating 表面镀层: Au or Sn over 50u" Ni 里镍外金 or 锡
 Electrical Characteristics 电气特性
 Current rating 额定电流: 2.5Amps
 Dielectric Withstanding Voltage 耐压: AC 1000V for 1 Minute.
 Insulator Resistance 绝缘电阻: 1000MΩ Min.
 Contact Resistance 接触电阻: 20MΩ Max.
 Operating Temperature 工作温度: -40℃~+105℃
 Max. Processing Temp 瞬时温度: 120℃ for 30-60 seconds (120℃ for 10 seconds)

未注尺寸公差			2.54-2*N		上海洲日电子有限公司	
尺寸	公差				Shanghai Zhouri Electronics CO.,LTD	
X.	±0.3	±5°			上海康司玛电子设备进出口有限公司	
XX	±0.2	±3°			Shanghai KangSiMa Electronic Equipment	
XXX	+0.15				Import and export Co.,LTD	
制图	周元金	201171018	版本编号	20171018 A/0	TEL:86-21-34975176/51571121	
审核	张海娜	201171018	图纸编号	ZR20171018-292		
核准	章妹	201171018	物料编号			
			第三视角			



1:1 mm 图幅 A4