



6	GROUND	STAINLESS	1	NATURAL
5	SHIELDING	BRASS STRIP	1	Ni PLATED
4	PIN	BRASS BAR	1	Ag PLATED
3	TERMINAL	STAINLESS	1	NAURAL
2	TIP SPRING	COPPER ALLOY	1	Ag PLATED
1	BODY	THERMOPLASTIC UL94V-0	1	BLACK
NO.	PARTS	MATERIAL	QTY.	FINISHING

PART NAME		DC POWER JACK				DRAWING	Y.C.ZHANG	DWG.No.	
PART NO.		DC-190-25				CHECK	G.C.Chen	REV.	A
	UNIT :	TOLERANCE OTHERWISE	UP TO 5	±0.2	ANGLE	APPROVAL		DATE	2019/03/01
	mm		ABOVE 5 ~30	±0.3		SCALE	3:1	PAGE	1 OF 1
			ABOVE 30	±0.5	0°±3°				
			ANGLE	±3°					