







PRODUCT NO.	DSWB03LHGETB
RohS compliant	




- Note:**
- All dimensions are in millimeters.
 - General tolerance: $\pm 0.2\text{mm}$.
 - Material:

- Base: UL94V-0 PBT Thermoplastic (Black).
- Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
- Actuators: UL94V-0 PBT Thermoplastic (White).
- Contact plating: Gold plating over nickel.
- Pitting material: Epoxy.

- Electrical
- Electrical: 2000 Operations per switch 24VDC, 25mA.
- Non-Switching Rating: 100mA, 50VDC.
- Switching Rating: 25mA, 24VDC
- Contact Resistance: 100 mΩ Max. at initial.

- Mechanical
- Mechanical life: 2000 Operations per switch.
- Stroke: 2.0mm.
- Operation Temp: -20°C to 70°C.
- Storage Temp: -40°C to 85°C.

6. PART NUMBER DESCRIPTION:



- 注意:**
- 波峰焊: 推荐焊锡温度在270°C $\pm 5^\circ\text{C}$, 浸锡时间为6~8秒。
 - 手工焊: 使用30瓦烙铁控制温度在320°C, 焊接时间大约2~3秒。
 - 拔柄位置: 产品焊接时, 请将产品的拔柄置于QRF端, 能给予产品更好的接触性能。
 - 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	
0 \pm 0.30	0 \pm 1°	[Symbol]	
.00 \pm 0.20	.0 \pm 0.5°	DRAWING	
.000 \pm 0.10	.000 \pm	DESIGN	
APPRO.		2013/07/02	
FILE NO. DSWB03LHGETB-A		PRODUCT FAMILY DSMB SERIES	
SIZE UNIT SCALE SHEET REV.		BY DSMB SERIES PITCH 2.54mm	
A4 mm FIT 1 OF 1 A		DongQuan Kingtek Industrial Co., Ltd	