








CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM

H	L
4.3	2.95
4.5	3.45
5.0	3.95
5.5	4.45
6.0	4.95
6.5	5.45
7.0	5.95
7.5	6.45
8.0	6.95
8.5	7.45
9.0	7.95
9.5	8.45
10.0	8.95



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	≥100MΩ
Contact resistance	≤50mΩ
Dielectric Strength	250 V 50HZ(1mm)
Travel	mm
Storage Temperature	- 30° C to 80° C

Mechanical

E	STEM	LCP	1	Maize
D	COVER	Phosphor copper	1	Silver
C	DDME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	Brass	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Type	Operating Force(gf)	Height mm	Button Shape(G,J,T)	Leads Ground pin (0,1)	Pegs Option (0,1)
YTS1K011	250±50	M 10.0	B (BLACK)	T	1 (Ground PIN) 0 (None)
		L 9.0			
		K 8.5			
		J 8.0			
		H 7.5			
YTS1K011	160±50	G 7.0	B (BLACK)	T	1 (Ground PIN) 0 (None)
		F 6.5			
		E 6.0			
		D 5.5			
		C 5.0			
YTS1K011	160±50	B 4.5	B (BLACK)	T	1 (Ground PIN) 0 (None)
		A 4.3			

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD


X.	±0.50	X.*	± 2°
.X	±0.30	.X*	± 1°
.XX	±0.10	.XX*	± 0.5°
.XXX	± 0.05		

UNITS	mm
MAT'L	
FINISH	
Q'TY	



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.	YTS1K011	TITLE:	TACTILE SWITCH 6x6 WATERPROOF
APPD:	ROGER	DWG NO.:	YTS1K011
CHKD:	RDC		
DR:	BILLY WANG 2020/08/21		



SCALE	SHEET	REV.
1/1	1/1	A1

Packaging: 1,000 pieces Bulks.