







CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	≥100MΩ
Contact resistance	≤50mΩ
Dielectric Strength	250 V 50HZ(1mm)
Travel	0.25mm
Storage Temperature	- 30° C to 80° C

Mechanical

E	STEM	LCP	1	Molze
D	COVER	Phosphor copper	1	Silver
C	DDOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	Brass	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/CO LOR

Type	Operating Force(gf)	Height mm	Button	Leads Shape (G,J,L,T)	Ground pin (0,1)	Pegs Option (0,1)
2	250±50	M 9.5	B (BLACK)	T	0 (None)	0 (None)
		L 9.0				
		K 8.5				
		J 8.0				
1	160±50	H 7.5	B (BLACK)	T	0 (None)	0 (None)
		G 7.0				
		F 6.5				
		E 6.0				
		D 5.5				
		C 5.0				
		B 4.5				
		A 4.3				

X. ±0.50	X.* ± 2°
.X ±0.30	.X* ± 1°
.XX ±0.10	.XX* ± 0.5°
.XXX ± 0.05	

UNITS mm
MAT'L
FINISH
Q'TY

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD



深圳市怡远科技有限公司

SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.
YTS1K016


TITLE:
TACTILE SWITCH

APPD: ROGER

DWG NO.:
YTS1K016

CHKD: RDC

DR: BILLY WANG 2020/08/21



SCALE	SHEET	REV.
1/1	1/1	A1