



X	
PART NO	vigor
2	G2
3	G3
4	G4
5	G5
6	G6
7	G7
8	G8



Specification:

1. Rating: DC 30V 50mA
2. Travel:  $2.5 \pm 0.1$ mm
3. Operating Force: A-B 150gf  $\pm 7.5$ gf  
B-A 150gf  $\pm 7.5$ gf
4. Contact Resistance: 100m $\Omega$  Max
5. Life: 10,000 Cycles Min



P.C.B Layout

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑤	Contact	1	Phosphor Bronze	Ag Plated
④	Terminal	3	Brass Strip	Ag Plated
③	Base	1	Phenolic Resin	Natural
②	Frame	1	STEEL STRIP	Ni Plated
①	Knob	1	POM	Black

APPROVALS		DATE
DRAWN	G.M.Chen	2014/11/25
CHECKED		
APPROVALS		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	SHEET	PROJ.
	A		NEW				30 $\pm 0.15$ 10 $\pm 0.10$ 5 $\pm 0.10$	$\pm 2^\circ$	mm	1:1	1 OF 1	

**DEALON** 德隆  
ELECTRONICS CO.,LTD

TITLE: VERTICAL SLIDE SWITCHES

PART NO. SS-12D01-GX