



**SPECIFICATIONS**

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer LCP、PA6T、UL94V-0  
PIN Brass Tin-plated  
Solder tad Phosphoric bronze Tin-plated



SECTION A-A

编号	尺寸 (mm)		
	A	B	C
HC-G1.0-2PLT	1.00	2.50	4.00
HC-G1.0-3PLT	2.00	3.50	5.00
HC-G1.0-4PLT	3.00	4.50	6.00
HC-G1.0-5PLT	4.00	5.50	7.00
HC-G1.0-6PLT	5.00	6.50	8.00
HC-G1.0-7PLT	6.00	7.50	9.00
HC-G1.0-8PLT	7.00	8.50	10.00
HC-G1.0-9PLT	8.00	9.50	11.00
HC-G1.0-10PLT	9.00	10.50	12.00
HC-G1.0-11PLT	10.00	11.50	13.00
HC-G1.0-12PLT	11.00	12.50	14.00

GENERAL TOLERANCE		制 图	钱岳生	料 号	HC-G1.0-NPLT	版本	A
X.±0.25	X.*±2°	DRAWING	2017、06、01	PART NO.	立 贴 WAFER SMT TYPE	REV.	
.X±0.20	.X*±1°	审 核	张 名	品 名		买 次	1/1
.XX±0.15	.XX*±0.5°	CHECK	2017、06、03	客 户 料 号	客户料号		
.XXX±0.10	.XXX*±0.5°	核 准	张 名	CUSTOMER NO.			
		APPROVAL	2017、06、05	<b>深圳市华灿天禄电子有限公司</b>			
		单 位	MM	比 例	1:1		
		UNITS		SCALE			