



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1500V AC/minute
 耐受电压: 1500V AC/分钟
 Temperature range:-25°C-+85°C
 温度范围: -25°C-+85°C
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 After environmental testing:≤30mΩ
 环境测试后: ≤30兆欧

X9555 T X - P XX X - X
 ① ②③ ④ ⑤ ⑥ ⑦

- 1.Series Number
- 2.Category:T-terminal
- 3.Shape:Blank-ordinary
- 4.Mstrial:P-Phosphor bronze
- 5.Plating style:G01-Contact Gold Flash
SN-Bright tin plating
- 6.Plating method:Blank-Stamping before plating
- 7.Mold No/Mark/Special No

X9555T-PG01	Phosphor Bronze	AWG#22-28	Stamping Before Pating:30u"Ni;Contact Area Gold Flash	X9555H
X9555T-PSN			Stamping Before Pating:30u"Ni;70u"Sn	
PART NO	Material	Wire Range	Finish	Suitable XKB Terminal

					units: mm	DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector		
					tolerance:	DWN		DATE		VIEW:	PART NO.:		
ΔX					X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	2.00mm Crimp Style Connectors		
ΔX					X.XX ±0.1mm	APPD		DATE		SIZE: A4	DWG NO.:		
ΔX					X.XXX ±0.05mm						X9555T-PXX		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											1.0g	1/1	A0