



Technical Data Material
 Contact Material: Brass/Phosphor Bronze
 Contact plating: Nicker/Gold Flash
 Insulator Material: Black Polyester UL94V-0
 Standard: PBT

Electrical
 Current rating: 3.0Amps/contact ma
 Contact resistance: 200m/contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding Voltage: 1000V AC/minute
 Mechanical
 Operating temperature: -40 C to $+105C$

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE	DEALON 德之隆® ELECTRONICS CO.,LTD	
DRAWN	G.M.Chen	2014/8/18	TITLE:	DETECTOR SWITCHES
CHECKED			PART NO.	M254D-02-135-B
APPROVALS			UNIT: mm	SCALE: 1:1
TOLERANCES ARE		±2°	DRAWING NO.	SHEET 1 OF 1
30 ^{±0.15}	±0.30	ANGLE		PROJ.
10 ^{±0.10}	±0.20			
5 ^{±0.10}	±0.15			