



Technical Data Material
 Contact Material: Brass/Phosphor Bronze
 Contact plating: Nicker/Gold Flash
 Insulator Material: Black Polyester UL94V-0
 Standard: PBT

Electrical
 Current rating: 3.0amps/contact ma
 Contact resistance: 200m/contact
 Insulation resistance: $\geq 1000M\Omega$ at $V=100V$
 Withstanding Voltage: 1000V AC/minute
 Mechanical
 Operating temperature: -40 C to $+105C$

APPROVALS		DATE	DEALON 德之隆® ELECTRONICS CO.,LTD		TITLE:	PART NO.	SCALE:	SHEET
DRAWN	G.M.Chen	2014/8/18			DETECTOR SWITCHES	M254D-02-065-B	1:1	1 OF 1
CHECKED								
APPROVALS								
TOLEFRANCES ARE		30 ^{±0.15}	±0.30	ANGLE	UNIT:	SCALE:	1:1	SHEET 1 OF 1
		10 ^{±0.10}	±0.20		mm			
		5 ^{±0.10}	±0.15	±2°	DRAWING NO.			PROJ.
ECN NO.	REV.	DATE.	DESCRIPTION.		CHANGE.	CHECK.	APPRO.	
	A		NEW					