



**Rating :** 16A 250V AC 3C  
**Insert And Extract Force:** 1.36kgf~6.8kgf  
**Terminal Strength:** ≥80N  
**Operating Life:** ≥5000 cycles  
**Withstand Voltage:** Between all terminals:2500VAC (50-60Hz)1min  
 terminals to Base:3750V AC (50-60Hz)1min  
 Leakage Current : 1mA  
**Insulation Resistance:** ≥100MΩ 500V DC  
**Body Material:** NYLON 66 94V-2-0

				普通公差 COMMON TOLERANCE :		深圳市华灿天禄电子有限公司					
				UP TO 5	±0.20	单位	mm	投影	Ac Inlet C20型	比例	Free
				ABOVE 5 TO 30	±0.30	UNIT		PROJECTED	品名	SCALE	
				ABOVE 30	±0.50	绘图	吴瑜	核对	型号		
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	±5°	日期	2014.4.26	核准	料号	DB-20	
						DATE		APPROVAL BY	料号	DB-20-5P-WW(1.5)	