





Specifications:

规格:

- Voltage rating:**30V AC/DC
- 额定电压: 30V AC/DC
- Current rating:**3A AC/DC
- 额定电流: 3A AC/DC
- Withstanding voltage:**150V AC/minute
- 耐受电压: 150V AC/分钟
- Temperature range:**-35°C-+85°C
- 温度范围: -35°C-+85°C
- Insulation resistance:** 1000MΩ min
- 绝缘电阻: 1000MΩ Min
- Contact resistance:**100mΩ Max
- 接触电阻: 100mΩ Max

X0813 F V S - XX X -LP V01
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No
2. Category:Female
3. Welding Board Angle:V-Straight 180°
4. Welding Way:S-SMT
5. Row No.Pin No:XX-06Pin-XXPin
6. High:A=0.59mm
Mating Height 0.6mm
7. Material:LP-LCP UL 94V-0 Black
8. Plating:V01-Gold Flash ;
SN-Tin Plating



X0813FVS-XXX-LPV01	LCP UL 94V-0	Copper Alloy	X0813W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

Recommended PCB Layout

广东星坤科技股份有限公司

日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR				±5°
L ≤ 4				±0.2
4 < L ≤ 16				±0.3
16 < L ≤ 63				±0.4
L > 63				±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE: 0.8mm BTB Style Connector
DWN	VIEW:	PART NO.: X0813FVS-XXX-LPV01
CHKD	UNIT: mm/in	DWG NO.: X-X0813FVS-XXX-LPV01
APPD	SIZE: A4	
	WEIGHT	SHEET
		1/1
	REVISION	A0