



Part No	Pin	A	B	C
WAFER-GH1.25-2PLB	2	1.25	5.75	3.75
WAFER-GH1.25-3PLB	3	2.50	7.00	5.00
WAFER-GH1.25-4PLB	4	3.75	8.25	6.25
WAFER-GH1.25-5PLB	5	5.00	9.50	7.50
WAFER-GH1.25-6PLB	6	6.25	10.75	8.75
WAFER-GH1.25-7PLB	7	7.50	12.00	10.00
WAFER-GH1.25-8PLB	8	8.75	13.25	11.25
WAFER-GH1.25-9PLB	9	10.00	14.50	12.50
WAFER-GH1.25-10PLB	10	11.25	15.75	13.75
WAFER-GH1.25-11PLB	11	12.50	17.00	15.00
WAFER-GH1.25-12PLB	12	13.75	18.25	16.25
WAFER-GH1.25-13PLB	13	15.00	19.50	17.50
WAFER-GH1.25-14PLB	14	16.25	20.75	18.75
WAFER-GH1.25-15PLB	15	17.50	22.00	20.00
WAFER-GH1.25-16PLB	16	18.75	23.25	21.25

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC,DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

MANUFACTURE DWG			东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WAFER GH1.25 立贴带扣	
DECIMALS:	ANGLES:	CUSTOMER COPY	PAR	WAFER-GH1.25-NPLB
X.:±0.2	X'.:±5°		DWN	
.X:±0.1	X.X':±3°		CHKD	
.XX:±0.05	X.XX':±1°	APVD		
		SCALE1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A