



Part No	Pin	A	B	C
WAFER-XH2.54-2PWB	2	2.50	10.00	8.30
WAFER-XH2.54-3PWB	3	5.00	12.50	10.80
WAFER-XH2.54-4PWB	4	7.50	15.00	13.30
WAFER-XH2.54-5PWB	5	10.00	17.50	15.80
WAFER-XH2.54-6PWB	6	12.50	20.00	18.30
WAFER-XH2.54-7PWB	7	15.00	22.50	20.80
WAFER-XH2.54-8PWB	8	17.50	25.00	23.30
WAFER-XH2.54-9PWB	9	20.00	27.50	25.80
WAFER-XH2.54-10PWB	10	22.50	30.00	28.30
WAFER-XH2.54-11PWB	11	25.00	32.50	30.80
WAFER-XH2.54-12PWB	12	27.50	35.00	33.30
WAFER-XH2.54-13PWB	13	30.00	37.50	35.80
WAFER-XH2.54-14PWB	14	32.50	40.00	38.30
WAFER-XH2.54-15PWB	15	35.00	42.50	40.80
WAFER-XH2.54-16PWB	16	37.50	45.00	43.30

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

MANUFACTURE DWG			 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WAFER 2.5 贴片	
DECIMALS:	ANGLES:		PAR	WAFER-XH2.54-NPWB
X.:±0.2	X'.:±5°		DWN	
.X:±0.1	X.X':±3°		CHKD	
.XX:±0.05	X.XX':±1°	APVD		
CUSTOMER COPY		SCALE1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A