










Main Specifications:

主要技术指标:

Climate grade: -30°C ~ + 80°C

气候等级: $-30^{\circ}\text{C} \sim +80$

Rated values: Max50 Ma12V, DC Min10
uA1V DC

额定值: Max50 Ma12V, DC Min10 uA1V DC

Contact resistance: $\leq 100\text{m } \Omega$

接触电阻: $\leq 100\text{m}\Omega$

Dielectric strength:250V AC 1Min

耐压: 250V AC 1Min

Insulation resistance: $\geq 100\text{M}\Omega$

绝缘电阻: $\geq 100\text{M}\Omega$

Travel: 0.20±0.10mm

行程: $0.20 \pm 0.10 \text{mm}$

Operating force: 160±50gf

操作力: 160±50gf

Life:200000

寿命: 200000

6	Upper cover 上盖	1	SUS 不锈钢	
5	Push Button 按钮	1	LCP	Black 黑色
4	Terminal 端子	1	Phosphor bronze 磷青铜	Silver plating 镀银
3	Yellow Membrane 黄膜	1	PI	Yellow 黄色
2	Shrapnel 弹片	1	SUS 不锈钢	Silver plating 镀银
1	Plastic base 塑胶底座	1	LCP	Black 黑色
NO	Name	PCS	Materials	Notes

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP10331615
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1					ROCPCU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION								
A		B		C	D	E	F	G			