




客户确认	
日期	

标记	版次	变更内容	日期
	A版	新版圈面	09-12-03
△	B版	增加线身印字说明	11-10-06
△	C版	线身印字“WINXIN”变更为“WINXIN”	14-4-24



Symbol 标号	Item 项目	Specification 规格
N	No. of Conductors (导体芯数)	6
P	Pitch (间距)	1.0±0.05
TP	Total Pitch (总间距)	5.0±0.10
W	Width (总宽度)	7.0±0.10
M	Margin (边缘宽度)	1.0±0.10
L	Total Length (总长度)	320±5
T	Insertion Thickness (插入厚度)	0.30±0.05
SI/S2	Conductor Strip Length (裸铜长度)	4/2±1.0
BI/B2	Supporting tape Length (补强板长度)	8/0±2.0
A1	Slanting (线口倾斜度)	<0.5

△△注：线身印字：WINXIN E230343 PU AWM 20798 80C 60V VW-1

**ELECTRICAL CHARACTERISTICS**

Conductor Resistance: JIS-C-3102(at20°C) 2.20Ω/1M Max.  
Insulation Resistance: Apply the voltage of DC 500V for one min 100MΩ Min.

Dielectric Strength: Apply AC 500V for one minute.  
Continuity Test: Apply microtest machine No Open/Short  
Rated voltage & temperature:UL Sub. 758VW-1

**Material**

Insulation: Flame Retardant Polyester  
Color: White  
Conductor: Copper with 1u m min. tin-Plating  
Supporting Tape: Flame Retardant Polyester  
Color: Blue

核准:	日期:	<p><b>深圳市灿科盟实业有限公司</b> Chantw CHANKEMENG INDUSTRYCO., LTD</p>			
业务:	日期:	<p>品名规格: FRC1.0-E-6*320-4/2-8/0</p>			
制图:	日期:	客户料号	BKD46*03210	单位	mm
L Y F	2014-4-24	图纸编号	S018900014	比例	/
		版本	C		WX00