



RECOMMENDED P.C.B LAYOUT

Specification

Insulator Material: Polyeset; UL94V-0

Standard: P.B.T

Contact Material: Brass

Contact plated: Gold Over Nickel

Poles: 2~40P (Double)

Current Rating : 3Amp

Contact Resistance: 20 Milliohms Max

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40℃ -- +105℃

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	深圳市灿科盟实业有限公司 KMITW CHANKEMENG INDUSTRY CO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
Jul-i-liu	2016-5-4	210S-2*5P 双翘 L=25MM
CLIENT P/N	SCALE	UNIT
	/	mm
FILE NO.	SCALE	free
S051400122		
REV.		A