



P. C. B. LAYOUT

**Specification**  
 Insulator Material: Polyeser, UL94V-0  
 Standard: PA6T  
 Contact Material: Brass  
 Contact plated: Gold Over Nickel  
 Poles: 2~40P  
 Current Rating : 3Amp  
 Contact Resistance: 20 Milliohms Max  
 Insulation Resistance : 1000MΩ Min.  
 Dielectric withstanding Voltage: AC 500V  
 Operation Temperature : -40°C -- +105°C

未注公差表	
XX	±0.2
XXX	±0.15
XXXX	±0.05

核准:	日期:	<p>深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD</p>
业务:	日期:	
制图:	日期:	品名规格: 210SMT-2*2P 双塑 (7.0/16.0/7.4)
SXA	2020-08-26	客户料号: C3025492
		单位: mm
		比例: /
		图纸编号: S051400138
		版本: A