



SPECIFICATIONS

Current rating: 2A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 30mΩ max.
 Withstand voltage: 800V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness:
 0.031"~0.063"(0.8~1.6)

Material:

Part No: 8-44
 Insulator: PA66 UL94V-2
 Contact: Brass
 Finish: Tin Plated

| Poles | Part No. | A | B | C |
|-------|----------------|------|------|------|
| 8 | 2008R-2*4P-1K | 6.0 | 9.0 | 10.0 |
| 10 | 2008R-2*6P-1K | 8.0 | 11.0 | 12.0 |
| 12 | 2008R-2*6P-1K | 10.0 | 13.0 | 14.0 |
| 14 | 2008R-2*7P-1K | 12.0 | 15.0 | 16.0 |
| 16 | 2008R-2*8P-1K | 14.0 | 17.0 | 18.0 |
| 18 | 2008R-2*8P-1K | 16.0 | 19.0 | 20.0 |
| 20 | 2008R-2*10P-1K | 18.0 | 21.0 | 22.0 |
| 22 | 2008R-2*11P-1K | 20.0 | 23.0 | 24.0 |
| 24 | 2008R-2*12P-1K | 22.0 | 25.0 | 26.0 |
| 26 | 2008R-2*13P-1K | 24.0 | 27.0 | 28.0 |
| 28 | 2008R-2*14P-1K | 26.0 | 29.0 | 30.0 |
| 30 | 2008R-2*15P-1K | 28.0 | 31.0 | 32.0 |
| 32 | 2008R-2*16P-1K | 30.0 | 33.0 | 34.0 |
| 34 | 2008R-2*17P-1K | 32.0 | 35.0 | 36.0 |
| 36 | 2008R-2*18P-1K | 34.0 | 37.0 | 38.0 |
| 38 | 2008R-2*19P-1K | 36.0 | 39.0 | 40.0 |
| 40 | 2008R-2*20P-1K | 38.0 | 41.0 | 42.0 |

TOLERANCE TABLE

| | |
|------|-------|
| .0 | ±0.30 |
| .00 | ±0.20 |
| .000 | ±0.05 |

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

LYP

2014-06-26


 深圳市凯途盟实业有限公司
 CHANKUO CHANKUO INDUSTRY CO., LTD

TITLE: 2008R-2*5P 带扣

| | |
|-----------|-----------------|
| PROD. P/N | C3025470 |
| UNIT | mm |
| SCALE | free |
| FILE NO. | W-2006R10P-B000 |
| REV. | A KL00 |