



Specification

1. Insulation Resistance: 1000 Megohms min.
2. Withstand Voltage: 1000V, AC/ minute
3. Durability: 600 mating cycles min.
4. Selective Gold-plating: (3;6;15;30;50) micro inch

3			
2	P1n	Phosphor Bronze	Gold-plating over Nickel
1	Housing	PBT	UL94V0 OR 94V2
NO.	PartName	QTY	MATERIAL

TOLERANCE TABLE

	.0	±0.30
	.00	±0.15
	.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
L.Y.F	2009-07-17

TITLE:		CLIENT P/N		SCALE		REV. A	
RJ45-8P/8C 全鍍 弯插 插口朝下		C3025489 (R-RJ45R08P-1011)		free		YH00	
CLIENT		UNIT		SCALE		REV.	
Cantw CHANKUANG INDUSTRIAL CO., LTD		mm		free		A YH00	
FILE NO.		UNIT		SCALE		REV.	
Cantw-RJ45-0027		mm		free		A YH00	

深圳市灿科盟实业有限公司
Cantw CHANKUANG INDUSTRIAL CO., LTD